HS-2 Laboratory Heat Sealer



PRECISION LABORATORY HEAT SEALER FOR ACCURATE AND REPEATABLE

DETERMINATION OF HEAT SEAL THRESHOLD. THE HS-2 IS ESTABLISHED AS THE 'INDUSTRY

STANDARD' FOR THIS PURPOSE. PRODUCES SEALS 5 TO 25MM WIDE AND UP TO 50MM LONG.



Benefits:

- Choose heat sealing bar configuration, either single (upper) or dual (upper & lower, meets ASTM F2029)
- User can easily change sealing bar for various surface areas or surface finishes
- Accurate and repeatable seals due to precision ground sealing faces and jaw guidance system
- Versatile applications for flexible materials, blister packs and pots
- Low Maintenance 12 months between calibrations

Features:

- Precise pressure calibration of standard surface area jaw face
- Temperature, pressure and dwell time digital controllers
- Jaws constructed in aluminium and silicone with precision ground faces
- Range of jaw face surfaces including Matched Crimp and Teflon Coating
- Auto cycle feature for greater user convenience with multiple samples



Sealing jaws: Flat metal, Rubber, Crimp or custom designed. Standard size 25mm wide x 50mm long. Can be specified any width 5mm to 25mm.



ASSURED QUALITY
TESTING SOLUTIONS



RDM Test Equipment Ltd Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK

> Tel: +44(0)1279 817171 Fax: +44(0)1279 815743 E-mail: sales@rdmtest.com Web: www.rdmtest.com

HS-2 Laboratory Heat Sealer



Specification

Seal Width 50 mm max.

Temperature Range: Ambient to 300°C, Accuracy: +/- 0.5%, Operating Accuracy: +/-2°C. Single (Upper) sealing jaw temperature control, or Dual

(Upper & Lower) sealing jaw temperature control

Pressure Range: 0 to 100psi (6.8bar, 689Kpa), via precision regulator and

digital display. Accuracy +/-5%, Repeatability +/- 0.02psi.

Supply via clean and dry compressed airline or bottled air/nitrogen

at 90 to 100psi

Dwell Time Range: 0.1 to 99.9 sec., Resolution 0.01 sec

Auto Cycle & Delay Time Range: 0.1 to 99.9 sec

Delay Time For automatic cycling of sealing bars used in manual production

environments. Assists with correct alignment of sample. Electronic

processor controlled.

Jaw Guidance

System

Dovetail slide on jaws with quick release mechanism.

Sealing Jaws Standard flat jaws 25mm x 50mm, constructed in aluminium with

precision ground face. Lower sealing jaw with precision ground

silicone rubber face. (See options below)

Environment 5-50°C ambient operating temperature,

RH 75% max (non-condensing)

Power 240V AC 50/60 Hz (110V AC voltage available

on request)

Options

- Single (Upper) sealing jaw temperature control or Dual (Upper & Lower)
 sealing jaw temperature control
- Sealing jaw dimension/profile as required (inc. Matched crimp 120° x
 1.8mm pitch)
- Stainless Steel sealing jaws
- Teflon Coated Tape or Teflon Coated Jaws
- Footswitch
- PVC Dust Cover
- Alarm package for temperature High/Low, selectable
- Cold seal system
- Digital thermometer with s/s band probe to check jaw temperature (see image)







RDM Test Equipment Ltd Unit 39 Golds Nurseries Bus. Park Jenkins Drive, ELSENHAM Hertfordshire, CM22 6JX, UK